

Graceful



P2544-0930K
shown with Medium Cherry blades



P2544-1530K
shown with Silver blades




P2544-2030K
shown with American Walnut blades

Refresh your living space with the crisp, clean style of the 54" Graceful fan. With a white opal glass shade and a 17W dimmable LED module, the five-blade fan comes with a remote control and is available in Brushed Nickel, Polished Chrome and Antique Bronze finishes. LED source offers a 3000K-color temperature, energy savings and maintenance benefits for the home.


FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20


P2544-0930K Brushed Nickel



P2544-1530K Polished Chrome



P2544-2030K Antique Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,454 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.

