

Olson

The 52" Olson ceiling fan features a generously sized etched watermark glass shade and sweeping blades highlighted with metal accents in a Brushed Nickel or Graphite finish. Two LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits. Olson features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light.

FINISHES

- Brushed Nickel - 09
- Graphite - 143

P2598-09 Brushed Nickel



Medium Cherry
Classic Walnut

P2598-143 Graphite



Gray Weathered Wood
Graphite



P2598-09
shown with Medium Cherry blades



P2598-143
shown with Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,023 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- Reversible plywood blades
- Etched watermark glass
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control, P2661-01 or P2662-01 hand-held remote control

SIZE

52" dia., 21-5/16" ht.
80" lead wires.

LAMP

Two Medium base LED lamps, 3000K, 90 CRI, 800 lumens, dimmable.

