

Gust



P2582-0930K
Shown with Silver blades

This five-blade 54" Gust ceiling fan features a white opal glass shade that is available in a Brushed Nickel, Graphite or Antique Bronze finish. A remote control is included. Gust has a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



P2582-2030K
Shown with Walnut blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

P2582-0930K Brushed Nickel



Silver

P2582-2030K Antique Bronze



Walnut

P2582-14330K Graphite



Graphite



P2582-14330K
Shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,242 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

