

# Fresno



P2548-0930K  
shown with Silver blades



P2548-2030K  
shown with Dark Walnut blades



P2548-3030K  
shown with White blades

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. A remote control with full range dimming and remote control is included.


## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30


### P2548-0930K Brushed Nickel



### P2548-2030K Antique Bronze



### P2548-3030K White



## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	5,718 cubic feet per minute
<b>Electricity Use</b>	79 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	80 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included, receiver mounted in motor.
- Remote control may be replaced with P2631-30 wall control

## SIZE

60" dia., 17-1/4" ht.  
80" lead wires.

## LAMP

18w LED Module, 3000K, 90 CRI,  
1400 lumens, dimmable.

