

# Tempt

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished Chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.

## FINISHES

- Polished Chrome - 15
- Antique Bronze - 20
- Vintage Brass - 163

### P2578-2030K Antique Bronze



Medium Cherry  
American Walnut

### P2578-1530K Polished Chrome



Medium Cherry  
Black

### P2578-16330K Vintage Brass



Dark Cherry  
Chesnut



P2578-1530K  
*shown with Black blades*



P2578-2030K  
*shown with American Walnut blades*



P2578-16330K  
*shown with Chesnut blades*

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,314 cubic feet per minute
<b>Electricity Use</b>	63 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	78 CFM/W



Remote Control Included  
*Three-speed fan operation*  
*Full-range dimming for light*

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

## SIZE

52" dia., 16-1/4" ht.  
80" lead wires.

## LAMP

17w LED Module, 3000K, 90 CRI,  
1400 lumens, dimmable.

