

Verada

This five-blade 52" Verada ceiling fan combines a linen glass shade with a 17W LED source. Available in a Brushed Nickel or Antique Bronze finish. Verada features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. LED light kit features a 3000K color temperature.



P2558-0930K
shown with white linen glass
and American Walnut blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2558-0930K Brushed Nickel



- Medium Cherry
- American Walnut

P2558-2030K Antique Bronze



- Medium Cherry
- American Walnut



P2558-2030K
shown with tea stained linen glass
and Medium Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,445 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	79 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood Blades
- Linen Glass shade
- 3 Speed pull chain switches
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 16" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.

