

Smyrna

This 52" Smyrna ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a clear hammered glass shade and contains a 17W dimmable 3000K LED module. Includes a wall control switch for fan speed and light operation.

FINISHES

- Antique Bronze - 20
- Forged Black - 80

P2576-2030K Antique Bronze



Walnut

P2576-8030K Forged Black



Toasted Oak



P2576-2030K
shown with Walnut blades



P2576-8030K
shown with Toasted Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,585 cubic feet per minute
Electricity Use	58 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- ABS all weather blades
- Clear Hammered glass shade
- Wet Location Rated

SIZE

52" dia., 19-1/2" ht.
80" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

