

# Montague



P2564-2030K  
shown with Walnut blades



P2564-3030K  
shown with White blades



P2564-8030K  
shown with Toasted Oak blades

This five-blade 60" Montague ceiling fan features an all weather wet location rating to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 18W dimmable, 3000K LED module, offering both form and function with energy and cost-savings benefits. A full function remote control is included.

## FINISHES


- Antique Bronze - 20
- White - 30
- Forged Black - 80

### P2564-2030K Antique Bronze



Walnut

### P2564-3030K White



White

### P2564-8030K Forged Black



Toasted Oak

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,693 cubic feet per minute
<b>Electricity Use</b>	75 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	96 CFM/W



Full Function Remote Control Included  
Three-speed fan operation  
Full-range dimming for light  
Reverse direction control

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- White Opal Glass Shade
- ABS all weather blades
- Wet Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

## SIZE

60" dia., 17-5/8" ht.  
80" lead wires.

## LAMP

18w LED Module,  
3000K, 90 CRI,  
1400 lumens, dimmable.

