

Lakehurst

This five-blade 60" Lakehurst ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. The Lakehurst fan will accept a universal outdoor rated light kit. Features a dual mount system and a three-speed pull chain fan switch.



P2562-20
shown with Walnut blades



P2562-30
shown with White blades



P2562-80
shown with Toasted Oak blades

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2562-20 Antique Bronze



Walnut

P2562-20 Antique Bronze



White

P2562-80 Forged Black



Toasted Oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,440 cubic feet per minute
Electricity Use	71 watts (excludes lights)
DOE Weighted CFM/W	105 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60" dia., 15-3/4" ht.
80" lead wires.

