

54" Patio Fan

FINISH

● Antique Bronze - 20

P2533-20 Antique Bronze



P2533-20
shown with Toasted Oak blades
* Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow 4,986 cubic feet per minute
Electricity Use 65 watts (excludes lights)
DOE Weighted CFM/W 74 CFM/W

FEATURES


- 30-year limited warranty
- 45° Canopy
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Wet location listed
- Compatible with universal light kits
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

54" dia., 18-1/4" ht.
 CTC 12-3/16 ht.
 80" lead wires.



CTC INSTALLATION





52" Patio Fan

P2502-20 Antique Bronze



P2502-30 White



P2502-30
shown with White blades



P2502-80
shown with Toasted Oak blades

P2502-80 Forged Black



P2502-141 Galvanized



P2502-141
shown with Silver blades



P2502-20
shown with Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow 4,991 cubic feet per minute
Electricity Use 64 watts (excludes lights)
DOE Weighted CFM/W 89 CFM/W

FEATURES

- 15-year limited warranty
- Dual Mount (flat or sloped ceiling-23°)
- Close-to-ceiling installation
- SureConnect® System
- Quick-Install canopy
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Wet location listed

SIZE

52" dia., 12-3/4" ht.
 CTC 9-11/16 ht.
 72" lead wires.



CTC INSTALLATION

