

# Vox Fan

Five-blade 52" Vox hugger-style ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade contains a 17W dimmable, 3000K LED module. A full function remote control is included. The fan mounts close to the ceiling and is available in popular Brushed Nickel, Antique Bronze and White finishes.

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

### P2572-0930K Brushed Nickel



### P2572-2030K Antique Bronze



### P2572-3030K White



P2572-0930K  
shown with Medium Cherry blades



P2572-2030K  
shown with American Walnut blades



P2572-3030K  
shown with White blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	4,276 cubic feet per minute
<b>Electricity Use</b>	62 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	76 CFM/W

## FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

## SIZE

52" dia., 11-5/8" ht.  
8" lead wires.

## LAMP

17w LED Module,  
3000K, 90 CRI,  
1400 lumens, dimmable.



Full Function Remote Control Included  
*Three-speed fan operation*  
*Full-range dimming for light*  
*Reverse direction control*