

Billows

With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes.




P2552-09
shown with Silver blades

FINISHES


- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Black - 80

P2552-09 Brushed Nickel




P2552-20
shown with American Walnut blades

P2552-20 Antique Bronze



P2552-80
shown with Toasted Oak blades

P2552-80 Forged Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,682 cubic feet per minute
Electricity Use	59 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-1/2" ht.
80" lead wires.

LAMP

Two medium base, 3000K, LED lamps included. 90 CRI, 800 lumens/lamp, dimmable (with added remote or wall control).

