

42" Builder Fan

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2500-09 Brushed Nickel



- Cherry
- Natural Cherry

P2500-20 Antique Bronze



- Classic Walnut
- Medium Cherry

P2500-30 White



- White
- Washed Oak



P2500-20
shown with Classic Walnut blades



P2500-09
shown with Cherry blades



P2500-09
shown with P2600-09WB light kit*
and with Cherry blades
* Light kit sold separately.



P2500-30
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 3,053 cubic feet per minute |
| Electricity Use | 46 watts (excludes lights) |
| DOE Weighted CFM/W | 64 CFM/W |

FEATURES

- 15-year limited warranty
- 23° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630 wall control or P2662-01 hand-held remote control

SIZE

42" dia., 12-3/8" ht.
CTC 8-5/16" ht.
72" lead wires.



CTC INSTALLATION

