

Shaffer

The 4-blade 56" Shaffer ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing, suitable for modern and urban industrial spaces. Available in Satin White with galvanized accents, Forged Black with chrome accents and Architectural Bronze with brushed bronze accents. Shaffer features a dual mount system and includes a remote control with batteries.




P2590-28
shown with Galvanized accents
and Silver blades

FINISHES

- Satin White - 28
- Forged Black - 80
- Architectural Bronze - 129


P2590-28 Satin White



P2590-80 Forged Black



P2590-129 Architectural Bronze



P2590-80
shown with Chrome accents
and Black blades



P2590-129
shown with Brushed Bronze accents
and Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,144 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	99 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56" dia., 16-1/4" ht.
80" lead wires.



Three-Speed Remote Control Included
Three-speed fan operation