

# POST TOP TRADITIONAL

## Traditional Post Top Luminaire

The PCPTT series offers a six sided traditional lantern design ideal for area and pedestrian lighting applications. Luminaire is offered in 2,000 to 8,000 lumen versions. All models standard as 4000K CCT.

MTO

Series	Wattage	Lumens	Distribution	Finish	Options
<b>PCPTT</b>	<b>27</b> - 27W	1925 - 1990	<b>3</b> - Type 3	<b>BZ</b> - Bronze	Blank
	<b>55</b> - 55W	3950 - 4050	<b>4</b> - Type 4	<b>BL</b> - Black	<b>P</b> - Photocell
	<b>80</b> - 80W	5905 - 6075	<b>5</b> - Type 5	<b>GN</b> - Green	
	<b>110</b> - 110W	7875 - 8100			

Size: 16-3/8" W., 29-13/16" ht.

