

# INDOOR/OUTDOOR REMOTE HEADS

The PERHC Series offers quality and value with a compact and attractive LED based remote emergency light. Source-heads are fully adjustable and glare-free. The remote Source are driven by the Progress remote capacity Exit combo or Emergency Light. The Outdoor Remote Source-heads are fully gasketed and weatherproof to ensure operation in wet environments. Can be used with PETPE, PE2EU, and PECUE remote capacity models.



PERHC-SG-ID-30



PERHC-DB-OD-30

Product No.	Finish	Location	Size	Source
<b>PERHC-SG-ID-30</b>	White	Indoor	4.6" W., 4.6" ht., 2.6" dia.	Single LED
<b>PERHC-DB-ID-30</b>			6.7" W., 4.7" ht., 2.5" dia.	Double LED
<b>PERHC-SG-OD-30</b>		Outdoor	4.5" W., 4.5" ht., 6.7" dia.	Single LED
<b>PERHC-DB-OD-30</b>			7.4" W., 4.5" ht., 5.6" dia.	Double LED