

NORMALLY ON/OFF OUTDOOR EMERGENCY

The PEOEU Series offers LED performance in “normally on” AC and emergency lighting modes. The unit has a prismatic polycarbonate refractor with a durable die-cast aluminum housing available with durable powder coated finish in dark bronze, nickel or white. The housing is fully sealed and gasketed. It is designed for wall mounting with a universal K/O pattern in the back-plate for installation to most standard size junction boxes. Illumination is provided by 2 high power LEDs driven at 3 watts each. LED color at 5500K.



PEOEU-EM-09



PEOEU-EM-20-HTR

Series	Description	Finish	Size	Source	Input
PEOEU-EM-09	Emergency Battery	Brushed Nickel	6.54" W., 10.47" ht., 3.78" dia.	LED, 223 lumens in AC mode, 5000K, 261 lumens in battery mode	120 or 277VAC, 50 or 60 Hz
PEOEU-EM-20		Bronze			
PEOEU-EM-30		White			
PEOEU-EM-09-HTR	Emergency Battery w/ heater option	Brushed Nickel			
PEOEU-EM-20-HTR		Bronze			
PEOEU-EM-30-HTR		White			