

# RECESSED PERFORMANCE

Product No.	Size	Source	Input
<b>PCICT-LED-22-30K</b>	23-7/8" L., 4" ht., 23-7/8" W.	35w LED, 3000K, 3500 Lumens	120 - 277V, 50 or 60 Hz
<b>PCICT-LED-22-35K</b>		35w LED, 3500K, 3700 Lumens	
<b>PCICT-LED-24-30K</b>	47-7/8" L., 4" ht., 23-7/8" W.	40w LED, 3000K, 4450 Lumens	
<b>PCICT-LED-24-35K</b>		40w LED, 3500K, 4800 Lumens	
<b>PLATLED22GU40</b>	23-7/8" L., 4" ht., 23-7/8" W.	29w LED, 4000K, 3200 Lumens	
<b>PLATLED24GU40</b>	47-7/8" L., 4" ht., 23-7/8" W.	42w LED, 4000K, 4700 Lumens	



PCICT-LED-22-30K



PCICT-LED-24-30K