

LOW PROFILE LENS STRIP

Product No.	Size	Source	Input
PCINS-LED-2-35K	24" L., 2-5/16" ht., 2-3/4" W.	18w LED, 3500K, 2000 Lumens	120 - 277V, 50 or 60 Hz
PCINS-LED-2-40K		18w LED, 4000K, 2000 Lumens	
PCINS-LED-4-35K	48" L., 2-5/16" ht., 2-3/4" W.	40w LED, 3500K, 4000 Lumens	
PCINS-LED-4-40K		40w LED, 4000K, 4000 Lumens	



PCINS-LED-2-35K



PCINS-LED-4-40K