


# 4" PRO-OPTIC®

## 4" New Construction Housing

CEILING OPENING	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	DESCRIPTION
5-3/8"	1-1/4"	1/2" and 3/4"	<b>P8064-EBG4</b>	4" New Construction Housing



P8064-EBG4

## 1100 Lumen Open Module Trims

PRODUCT NO.	DESCRIPTION
<b>P8067-21A/30KG4</b>	Clear Alzak'
<b>P8067-21A/35KG4</b>	Clear Alzak'
<b>P8067-21A/40KG4</b>	Clear Alzak'
<b>P8067-22A/30KG4</b>	Gold Alzak'
<b>P8067-22A/35KG4</b>	Gold Alzak'
<b>P8067-22A/40KG4</b>	Gold Alzak'
<b>P8067-28/30KG4</b>	White
<b>P8067-28/35KG4</b>	White
<b>P8067-28/40KG4</b>	White



### LED FEATURES

- Universal 120 - 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)

## 2000 Lumen Open Module Trims

PRODUCT NO.	DESCRIPTION
<b>P8206-21A/30KG4</b>	Clear Alzak'
<b>P8206-21A/35KG4</b>	Clear Alzak'
<b>P8206-21A/40KG4</b>	Clear Alzak'
<b>P8206-22A/30KG4</b>	Gold Alzak'
<b>P8206-22A/35KG4</b>	Gold Alzak'
<b>P8206-22A/40KG4</b>	Gold Alzak'
<b>P8206-28/30KG4</b>	White
<b>P8206-28/35KG4</b>	White
<b>P8206-28/40KG4</b>	White



- Light commercial bar hangers included
- Suitable for wet locations, non-IC rated
- 5 year warranty

# 6" PRO-OPTIC®

## 6" New Construction Housing

CEILING OPENING	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	DESCRIPTION
6-1/4"	1-1/4"	1/2" and 3/4"	<b>P8216-EB</b> <b>P8216-DM</b> <b>P8216-277EB</b> <b>P8216-277DM</b>	Built to order with a 2-4 week lead time



## 900 Lumen Open Module Trims

<b>P8104-2830K</b>
<b>P8104-2835K</b>
<b>P8104-2840K</b>



### LED FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.

## 1300 Lumen Open Module Trims

<b>P8105-2830K</b>
<b>P8105-2835K</b>
<b>P8105-2840K</b>



## 1500 Lumen Open Module Trims

<b>P8106-2830K</b>
<b>P8106-2835K</b>
<b>P8106-2840K</b>



- Suitable for wet locations, non-IC rated
- 5 year warranty

# 6" PRO-OPTIC®

CEILING OPENING	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	DESCRIPTION
6-1/4"	1-1/4"	1/2" and 3/4"	<b>P8023-EBG4</b>	New Construction
Min. 5-16/16". Max. 6-1/8".	1-1/2"	1/2" and 3/4"	<b>P8002-EBG4</b>	Retrofit
Min. 5-16/16". Max. 6-1/8".	1-1/2"	1/2" and 3/4"	<b>P8002-EBSDG4</b>	Small Diameter Retrofit



### LED FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty

## 1100 Lumen Open Module Trims

PRODUCT NO.	DESCRIPTION
<b>P8021-21A/30KG4</b>	Clear Alzak'
<b>P8021-21A/35KG4</b>	Clear Alzak'
<b>P8021-21A/40KG4</b>	Clear Alzak'
<b>P8021-22A/30KG4</b>	Gold Alzak'
<b>P8021-22A/35KG4</b>	Gold Alzak'
<b>P8021-22A/40KG4</b>	Gold Alzak'
<b>P8021-28/30KG4</b>	White
<b>P8021-28/35KG4</b>	White
<b>P8021-28/40KG4</b>	White



## 1100 Lumen Open Module Trims - Wide Flange

PRODUCT NO.	DESCRIPTION
<b>P8021-21A/30KWFG4</b>	Clear Alzak'
<b>P8021-21A/35KWFG4</b>	Clear Alzak'
<b>P8021-21A/35KWFG4</b>	Clear Alzak'
<b>P8021-22A/30KWFG4</b>	Gold Alzak'
<b>P8021-22A/35KWFG4</b>	Gold Alzak'
<b>P8021-22A/35KWFG4</b>	Gold Alzak'
<b>P8021-28/30KWFG4</b>	White
<b>P8021-28/35KWFG4</b>	White
<b>P8021-28/35KWFG4</b>	White



## 2000 Lumen Open Module Trims

PRODUCT NO.	DESCRIPTION
<b>P8050-21A/30KG4</b>	Clear Alzak'
<b>P8050-21A/35KG4</b>	Clear Alzak'
<b>P8050-21A/40KG4</b>	Clear Alzak'
<b>P8050-22A/30KG4</b>	Gold Alzak'
<b>P8050-22A/35KG4</b>	Gold Alzak'
<b>P8050-22A/40KG4</b>	Gold Alzak'
<b>P8050-28/30KG4</b>	White
<b>P8050-28/35KG4</b>	White
<b>P8050-28/40KG4</b>	White




## 2000 Lumen Open Module Trims - Wide Flange

PRODUCT NO.	DESCRIPTION
<b>P8050-21A/30KWFG4</b>	Clear Alzak'
<b>P8050-21A/35KWFG4</b>	Clear Alzak'
<b>P8050-21A/40KWFG4</b>	Clear Alzak'
<b>P8050-22A/30KWFG4</b>	Gold Alzak'
<b>P8050-22A/35KWFG4</b>	Gold Alzak'
<b>P8050-22A/40KWFG4</b>	Gold Alzak'
<b>P8050-28/30KWFG4</b>	White
<b>P8050-28/35KWFG4</b>	White
<b>P8050-28/40KWFG4</b>	White



# 6" PRO-OPTIC® - HIGH LUMEN

CEILING OPENING	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	DESCRIPTION
6-1/4"	1-1/4"	1/2" and 3/4"	<b>P8212-EB120VG4</b>	New Construction 120V
Min. 5-16/16". Max. 6-1/8".	1-1/2"	1/2" and 3/4"	<b>P8212-EB277VG4</b>	New Construction 277V
Min. 5-16/16". Max. 6-1/8".	1-1/2"	1/2" and 3/4"	<b>P8214-EB120VG4</b>	Retrofit 120V
			<b>P8214-EB277VG4</b>	Retrofit 277V
			<b>P8214-EBSD120VG4</b>	Retrofit 120V
			<b>P8214-EBSD277VG4</b>	Retrofit 277V



### LED FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty

## 2800 Lumen Open Module Trims

PRODUCT NO.	DESCRIPTION
<b>P8112-21A/30KG4</b>	Clear Alzak'
<b>P8112-21A/35KG4</b>	Clear Alzak'
<b>P8112-21A/40KG4</b>	Clear Alzak'
<b>P8112-22A/30KG4</b>	Gold Alzak'
<b>P8112-22A/35KG4</b>	Gold Alzak'
<b>P8112-22A/40KG4</b>	Gold Alzak'
<b>P8112-28/30KG4</b>	White
<b>P8112-28/35KG4</b>	White
<b>P8112-28/40KG4</b>	White



## 2800 Lumen Open Module Trims - Wide Flange

PRODUCT NO.	DESCRIPTION
<b>P8112-21A/30KWFG4</b>	Clear Alzak'
<b>P8112-21A/35KWFG4</b>	Clear Alzak'
<b>P8112-21A/40KWFG4</b>	Clear Alzak'
<b>P8112-22A/30KWFG4</b>	Gold Alzak'
<b>P8112-22A/35KWFG4</b>	Gold Alzak'
<b>P8112-22A/40KWFG4</b>	Gold Alzak'
<b>P8112-28/30KWFG4</b>	White
<b>P8112-28/35KWFG4</b>	White
<b>P8112-28/40KWFG4</b>	White



# 6" PRO-OPTIC® - WALL WASH

CEILING OPENING	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	DESCRIPTION
6-1/4"	1-1/4"	1/2" and 3/4"	<b>P8005-EBG4</b>	New Construction Wall Wash 110 & 2000 Lumens



- LED FEATURES**
- 120V or 277V high efficiency driver
  - Remote phosphor technology for controlled color consistency
  - 3000K, 3500K and 4000K options
  - 80+ CRI
  - 50 lumens per watt fixture efficacy
  - TM-21 50,000 hour life
  - J-box rated for (8) #12 90° conductors (4 in/4 out)
  - Light commercial bar hangers incl.
  - Suitable for damp locations, non-IC rated
  - 5 year warranty

## 1100 Lumen Open Module Trims

- P8006-21A/30KG4**  
**P8006-21A/35KG4**  
**P8006-21A/40KG4**  
Clear Alzak'



- P8006-22A/30KG4**  
**P8006-22A/35KG4**  
**P8006-22A/40KG4**  
Gold Alzak'



## 2000 Lumen Open Module Trims

- P8051-21A/30KG4**  
**P8051-21A/35KG4**  
**P8051-21A/40KG4**  
Clear Alzak'



- P8051-22A/30KG4**  
**P8051-22A/35KG4**  
**P8051-22A/40KG4**  
Gold Alzak'



# 6" PRO-OPTIC® - HIGH LUMEN WALL WASH

CEILING OPENING	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	DESCRIPTION
6-1/4"	1-1/4"	1/2" and 3/4"	<b>P8223-EB120VG4</b> <b>P8223-EB277VG4</b>	New Construction 120V New Construction 277V Wall Wash



- LED FEATURES**
- 120V or 277V high efficiency driver
  - Remote phosphor technology for controlled color consistency
  - 3000K, 3500K and 4000K options
  - 80+ CRI
  - 50 lumens per watt fixture efficacy
  - TM-21 50,000 hour life
  - J-box rated for (8) #12 90° conductors (4 in/4 out)
  - Light commercial bar hangers incl.
  - Suitable for damp locations, non-IC rated
  - 5 year warranty

## 2800 Lumen Open Module Trims

- P8123-21A/30KG4**  
**P8123-21A/35KG4**  
**P8123-21A/40KG4**  
Clear Alzak'



- P8123-22A/30KG4**  
**P8123-22A/35KG4**  
**P8123-22A/40KG4**  
Gold Alzak'



- P8123-28/30KG4**  
**P8123-28/35KG4**  
**P8123-28/40KG4**  
White



# 8" PRO-OPTIC®

## 8" New Construction and Retrofit Housing

PLASTER FRAME	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	CEILING OPENING
9"x13-3/4" to 16"	1-1/4"	1/2" and 3/4"	<b>P8102-EBG4</b>	Min. 8-1/8". Max. 8-3/4".
9"x13-3/4" to 16"	1-1/4"	1/2" and 3/4"	<b>P8102-EBSDG4</b>	Min. 7-5/16". Max. 8-1/8".
9"x15-1/2"	1-1/4"	1/2" and 3/4"	<b>P8103-EBG4</b>	8" New Construction



- LED FEATURES**
- 120V or 277V high efficiency driver
  - Remote phosphor technology for controlled color consistency
  - 3000K, 3500K and 4000K options
  - 80+ CRI
  - 50 lumens per watt fixture efficacy
  - TM-21 50,000 hour life
  - J-box rated for (8) #12 90° conductors (4 in/4 out)
  - Light commercial bar hangers incl.
  - Suitable for wet locations, non-IC rated
  - 5 year warranty



## 1100 Lumen Open Module Trims - EB

- P8121-21A/30KG4**  
**P8121-21A/35KG4**  
**P8121-21A/40KG4**  
Clear Alzak'
- P8121-22A/30KG4**  
**P8121-22A/35KG4**  
**P8121-22A/40KG4**  
Gold Alzak'
- P8121-28/30KG4**  
**P8121-28/35KG4**  
**P8121-28/40KG4**  
White



## 1100 Lumen Open Module Trims - EBSD

- P8121-21A/30KWFG4**  
**P8121-21A/35KWFG4**  
**P8121-21A/40KWFG4**  
Clear Alzak'
- P8121-22A/30KWFG4**  
**P8121-22A/35KWFG4**  
**P8121-22A/40KWFG4**  
Gold Alzak'
- P8121-28/30KWFG4**  
**P8121-28/35KWFG4**  
**P8121-28/40KWFG4**  
White



## 2000 Lumen Open Module Trims - EB

- P8133-21A/30KG4**  
**P8133-21A/35KG4**  
**P8133-21A/40KG4**  
Clear Alzak'
- P8133-22A/30KG4**  
**P8133-22A/35KG4**  
**P8133-22A/40KG4**  
Gold Alzak'
- P8133-28/30KG4**  
**P8133-28/35KG4**  
**P8133-28/40KG4**  
White



## 2000 Lumen Open Module Trims - EBSD

- P8133-21A/30KWFG4**  
**P8133-21A/35KWFG4**  
**P8133-21A/40KWFG4**  
Clear Alzak'
- P8133-22A/30KWFG4**  
**P8133-22A/35KWFG4**  
**P8133-22A/40KWFG4**  
Gold Alzak'
- P8133-28/30KWFG4**  
**P8133-28/35KWFG4**  
**P8133-28/40KWFG4**  
White



# 8" PRO-OPTIC®

## 8" New Construction and Retrofit Housing - High Lumen

PLASTER FRAME	CEILING THICKNESS	PRYOUTS	PRODUCT NO.	CEILING OPENING
9"x13-3/4" to 16"	1-1/4"	1/2" and 3/4"	<b>P8215-EB120VG4</b> <b>P8215-EB277VG4</b>	Min. 8-1/8". Max. 8-3/4".
			<b>P8215-EBSD120VG4</b> <b>P8215-EBSD277VG4</b>	Min. 7-5/16". Max. 8-1/8".
			<b>P8220-EB120VG4</b> <b>P8220-EB277VG4</b>	8" New Construction



### LED FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty

### 3000 Lumen Open Module Trims - EB

<b>P8120-21A/30KG4</b>	<b>P8120-22A/30KG4</b>	<b>P8120-28/30KG4</b>
<b>P8120-21A/35KG4</b>	<b>P8120-22A/35KG4</b>	<b>P8120-28/35KG4</b>
<b>P8120-21A/40KG4</b>	<b>P8120-22A/40KG4</b>	<b>P8120-28/40KG4</b>
Clear Alzak®	Gold Alzak®	White



### 3000 Lumen Open Module Trims - EBSD

<b>P8120-21A/30KWFG4</b>	<b>P8120-22A/30KWFG4</b>	<b>P8120-28/30KWFG4</b>
<b>P8120-21A/35KWFG4</b>	<b>P8120-22A/35KWFG4</b>	<b>P8120-28/35KWFG4</b>
<b>P8120-21A/40KWFG4</b>	<b>P8120-22A/40KWFG4</b>	<b>P8120-28/40KWFG4</b>
Clear Alzak®	Gold Alzak®	White



Featuring 8" Pro-Optic®