


# HANGAR

Fixtures in the Hangar collection are fun, light and airy pieces – perfect for both casual and modern homes. A sophisticated, statement-making frame occupies a large visual space. Modern wire basket forms are finished in Brushed Nickel with graphite accents or Antique Bronze and natural brass accents to complete the design.



P500117-009

P500115-009  
shown with P7825-01  
vintage lamp



P400105-009  
shown with P7827-01  
vintage lamp



P400106-009  
shown with P7825-01  
vintage lamp



**FINISHES**  
● Brushed Nickel - 009



P710043-009

**SEMI-FLUSH CONVERTIBLE**  
**P350102-009** Brushed Nickel  
Hanging and ceiling mount hardware included. Vintage Linen Shade.  
16" dia., 13-1/4" ht.  
Overall ht. w/stem 78-1/2", wire 10'.  
Two medium base lamps,  
each 60w max.



P350102-009

**FIVE-LIGHT CHANDELIER**  
**P400105-009** Brushed Nickel  
30" dia., 19-3/4" ht.  
Overall ht. w/stem 77", wire 15'.  
Five medium base lamps,  
each 60w max.

**EIGHT-LIGHT CHANDELIER**  
**P400106-009** Brushed Nickel  
40" dia., 24-7/8" ht.  
Overall ht. w/stem 91-1/2", wire 15'.  
Eight medium base lamps,  
each 60w max.

**MINI-PENDANT**  
**P500115-009** Brushed Nickel  
13" dia., 9-5/8" ht.  
Overall ht. w/stem 76-1/2", wire 10'.  
One medium base lamp,  
60w max.

**ONE-LIGHT PENDANT**  
**P500116-009** Brushed Nickel  
Vintage Linen Shade.  
20" dia., 26" ht.  
Overall ht. w/stem 92", wire 15'.  
One medium base lamp,  
100w max.



P500116-009

**THREE-LIGHT PENDANT**  
**P500117-009** Brushed Nickel  
Vintage Linen Shade.  
24" dia., 24-1/4" ht.  
Overall ht. w/stem 90", wire 15'.  
Three medium base lamps,  
each 75w max.

**WALL BRACKET**  
**P710043-009** Brushed Nickel  
5" W., 8-3/4" ht.  
Extends 4-1/2". H/CTR 4".  
One medium base lamp,  
60w max.

# HANGAR

## FINISHES

- Antique Bronze - 020

## SEMI-FLUSH CONVERTIBLE

**P350102-020** Brushed Nickel  
Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht. Overall ht. w/stem 78-1/2", wire 10'. Two medium base lamps, each 60w max.



P710043-020

## FIVE-LIGHT CHANDELIER

**P400105-020** Antique Bronze  
30" dia., 19-3/4" ht. Overall ht. w/stem 77", wire 15'. Five medium base lamps, each 60w max.



P400105-020  
shown with P7825-01  
vintage lamp



P350102-020

## EIGHT-LIGHT CHANDELIER

**P400106-020** Antique Bronze  
40" dia., 24-7/8" ht. Overall ht. w/stem 91-1/2", wire 15'. Eight medium base lamps, each 60w max.



P400106-020  
shown with P7827-01  
vintage lamp



P500116-020

## MINI-PENDANT

**P500115-020** Antique Bronze  
13" dia., 9-5/8" ht. Overall ht. w/stem 76-1/2", wire 10'. One medium base lamp, 60w max.

## ONE-LIGHT PENDANT

**P500116-020** Antique Bronze  
Vintage Linen Shade. 20" dia., 26" ht. Overall ht. w/stem 92", wire 15'. One medium base lamp, 100w max.

## THREE-LIGHT PENDANT

**P500117-020** Antique Bronze  
Vintage Linen Shade. 24" dia., 24-1/4" ht. Overall ht. w/stem 90", wire 15'. Three medium base lamps, each 75w max.

## WALL BRACKET

**P710043-020** Antique Bronze  
5" W., 8-3/4" ht. Extends 4-1/2". H/CTR 4". One medium base lamp, 60w max.



P500117-020