

FONTAYNE

With updated designs that honor the charm of early American styling, Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations include Antique Bronze with faux oak accents or Brushed Nickel with weathered gray accents.



P400080-020



P400080-020



P500088-020



P400081-020



P500089-020



P400083-020



P400082-020

FINISHES

- Antique Bronze - 020

FOUR-LIGHT CHANDELIER

P400080-020 Antique Bronze
15-3/4" dia., 30" ht.
Overall ht. w/chain 105", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400081-020 Antique Bronze
22" dia., 24-3/4" ht.
Overall ht. w/chain 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

SIX-LIGHT LINEAR CHANDELIER

P400082-020 Antique Bronze
36" W., 22" L., 15-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400083-020 Antique Bronze
32" dia., 28-3/4" ht.
Overall ht. w/chain 107", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-020 Antique Bronze
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500089-020 Antique Bronze
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps*

FONTAYNE

FINISHES

● Brushed Nickel - 009

FOUR-LIGHT CHANDELIER

P400080-009 Brushed Nickel
15-3/4" dia., 30" ht.
Overall ht. w/chain 105", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400081-009 Brushed Nickel
22" dia., 24-3/4" ht.
Overall ht. w/chain 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

SIX-LIGHT LINEAR CHANDELIER

P400082-009 Brushed Nickel
36" W., 22" L., 15-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400083-009 Brushed Nickel
32" dia., 28-3/4" ht.
Overall ht. w/chain 107", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-009 Brushed Nickel
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500089-009 Brushed Nickel
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps*



P400080-009



P400080-009



P500088-009



P400081-009



P500089-009



P400083-009



P400082-009