

# SAVOR

Savor is a soft blend of sweeping details and contemporized wrought iron craftsmanship making it suitable for a wide variety of home décor styles. Sheer sailcloth textured shades are integral to the design.



P400075-134



P350092-134



P500080-134



P500081-134



P400075-134



P710029-134



P400076-134

## FINISH

● Silver Ridge - 134

## SEMI-FLUSH CONVERTIBLE

**P350092-134** Silver Ridge  
Hanging and ceiling mount hardware included.  
17" dia., 15-1/2" ht.  
Overall ht. w/chain 56-1/2", wire 10'.  
Four candelabra base lamps, each 60w max.

## SIX-LIGHT CHANDELIER

**P400075-134** Silver Ridge  
33" dia., 27-1/2" ht.  
Overall ht. w/chain 102-1/2", wire 15'.  
Six candelabra base lamps, each 60w max.

## TEN-LIGHT CHANDELIER

**P400076-134** Silver Ridge  
38" dia., 35-3/4" ht.  
Overall ht. w/chain 159", wire 15'.  
Ten candelabra base lamps, each 60w max.

## MINI-PENDANT

**P500080-134** Silver Ridge  
10" dia., 14-1/2" ht.  
Overall ht. w/stem 80-1/2", wire 10'.  
One medium base lamp, 100w max.

## SIX-LIGHT PENDANT

**P500081-134** Silver Ridge  
24" dia., 25-1/4" ht.  
Overall ht. w/chain 100-1/2", wire 15'.  
Six candelabra base lamps, each 60w max.

## WALL BRACKET

**P710029-134** Silver Ridge  
6-5/8" W., 18" ht.  
Extends 8". H/CTR 9".  
One candelabra base lamp, 60w max.