

# STRATHAM

Stratham's signature focal point features a sparkly string of alternating drops of cylindrical and crystal orb beads. Large in scale, while delicate in details, the chandelier and semi-flush options showcase a stunning, faceted K9 glass column. Upward arching candelabra arms feature a soft Brushed Nickel finish and add visual interest for a variety of applications. Off white silk shades available separately for chandelier and semi-flush fixtures.



P400160-009  
shown w/ P8704-01



P710053-009

**FINISH**  
● Brushed Nickel - 009

**SEMI-FLUSH CONVERTIBLE**  
**P350118-009** Brushed Nickel  
Hanging and ceiling mount hardware included.  
19" dia., 16-3/4" ht.  
Overall ht. w/chain 56", wire 10'.  
Four candelabra base lamps, each 60w max.



P350118-009  
shown as semi-flush



P400160-009

**FIVE-LIGHT CHANDELIER**  
**P400160-009** Brushed Nickel  
27-1/4" dia., 25-1/2" ht.  
Overall ht. w/chain 101", wire 15'.  
Five candelabra base lamps, each 60w max.

**NINE-LIGHT CHANDELIER**  
**P400161-009** Brushed Nickel  
Two-tier.  
35-1/8" dia., 42" ht.  
Overall ht. w/chain 164-1/2", wire 15'.  
Nine candelabra base lamps, each 60w max.



P350118-009



P400161-009

**ONE-LIGHT WALL BRACKET**  
**P710053-009** Brushed Nickel  
4-1/2" W., 14-1/8" ht.  
Extends 5-3/4". H/CTR 6-3/4".  
1 candelabra base lamp, 60w max.

**ACCESSORY SHADE**  
**P8704-01** White Fabric  
1" uno-style fitter.  
5-1/2" dia., 4-3/4" ht.



P8704-01