

SPRINGER



P250000-129 shown with Distressed Walnut blades

P250000-081

Antique Nickel shown
with White Barnwood blades



White Barnwood



P250000-129

Architectural Bronze shown
with Distressed Walnut blades



Distressed Walnut



Springer is a statement-making ceiling fan with a rustic flair. The 12-blade, 60" ceiling fan was inspired by the form and function of a windmill and is ideal for Farmhouse, Industrial and Transitional interior settings. A full function remote control with batteries is included along with a dual mount canopy that accommodates flat or sloped ceilings.

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- Plywood blades
- Full function remote control with batteries is included

SIZE

60" dia., 17-3/8" ht.
80" lead wires

FINISHES

- Architectural Bronze - 129
- Antique Nickel - 081

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	6,377 cubic feet per minute
ELECTRICITY USE:	33 watts (excludes lights)
AIRFLOW EFFICIENCY:	193 cubic feet per minute per watt



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

PROGRESSLIGHTING.COM



Canada



Fan



Dry
Indoor only