

CULLMAN

Cullman outdoor lanterns deliver dramatic scale with Craftsman appeal. Bold and linear details in an Antique Bronze finish highlight clear seeded glass. Ideal for spacious Modern architecture settings. Available in post, hanging and wall lantern options.



P560125-020



P540018-020



P550045-020



P560124-020



P560125-020



P560126-020

OUTDOOR

FINISH

● Antique Bronze - 020

POST LANTERN

P540018-020 Antique Bronze
11" sq., 22-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550045-020 Antique Bronze
11" sq., 19-5/8" ht.
Overall ht. w/chain 94", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560124-020 Antique Bronze
7" W., 16-5/8" ht.
Extends 8-3/8". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560125-020 Antique Bronze
9" W., 16" ht.
Extends 10-3/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560126-020 Antique Bronze
11" W., 19-1/4" ht.
Extends 12-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.