

RIGSBY

The use of mixed media highlights a variety of elegant details featured in Rigsby. A hint of faux marble appears in the horizontal cross bars, while Vintage Gold and Chrome accents create a dual toned finish. Decorated white gloss hardback shades – lined with burnished gold foil – complete the fixture. Inspired by mid-century design influences, this distinct and classic collection is suitable for Modern and Luxe interiors.



P500175-078



P350128-078



P350128-078
shown as semi-flush



P300201-078



P500175-078



P400172-078



P400173-078

FINISH

● Vintage Gold - 078

WALL BRACKET

P300201-078 Vintage Gold
6" W., 13-1/4" ht.
Extends 9-5/8". H/CTR 7-1/2".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350128-078 Vintage Gold
Hanging and ceiling mount
hardware included.
18" dia., 11-3/4" ht.
Overall ht. w/chain 52", wire 10'.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400172-078 Vintage Gold
32" dia., 16-3/4" ht.
Overall ht. w/chain 92", wire 15".
Five medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400173-078 Vintage Gold
Two-tier.
36" dia. 26-1/4" ht.
Overall ht. w/chain 149-1/2", wire 15'.
Nine medium base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500175-078 Vintage Gold
22" dia., 12-1/4" ht.
Overall ht. w/chain 81", wire 10'.
Four medium base lamps,
each 60w max.