

# BLAKELY

The Blakely collection has two unique and fashion-forward design styles. Choose between a rectangular frame or an open linear form. Both styles celebrate geometric interplay with clean, straight lines. Finished in Graphite with satin brass accents, the Blakely collection is ideal for Modern and Traditional interiors.



P500168-143



P350120-143



P350120-143  
shown as semi-flush



P500168-143



P400086-143

**FINISH**

- Graphite - 143

**SEMI-FLUSH CONVERTIBLE**

**P350120-143** Graphite  
Hanging and ceiling mount hardware included.  
17-1/4" W., 9-3/8" ht.  
Overall ht. w/chain 74-1/2", wire 10'.  
Two medium base lamps, each 60w max.

**FOUR-LIGHT ISLAND**

**P400086-143** Graphite  
40-7/8" W., 17-1/4" ht., 11" depth.  
Overall ht. w/stem 82-1/2", wire 15'.  
Four medium base lamps, each 60w max.

**FOUR-LIGHT PENDANT**

**P500168-143** Graphite  
23-1/4" W., 25-3/4" ht.  
Overall ht. w/stem 91-1/2", wire 15'.  
Four medium base lamps, each 60w max.

# BLAKELY

## FINISHES

- Brushed Nickel - 009
- Polished Nickel - 104
- Brushed Bronze - 109
- Graphite - 143

## TWO-LIGHT WALL BRACKET

**P300214-143** Graphite  
 8-1/4" W., 9-3/8" ht.  
 Extends 4-7/8". H/CTR 5-5/8".  
 Two candelabra base lamps,  
 each 60w max.

## TWO-LIGHT FLUSH MOUNT

**P350121-009** Brushed Nickel  
**P350121-104** Polished Nickel  
**P350121-109** Brushed Bronze  
 13-5/8" dia., 5-3/4" ht.  
 Two medium base lamps,  
 each 60w max.

## FOUR-LIGHT CHANDELIER

**P400179-143** Graphite  
 20" W., 15-5/8" ht.  
 Overall ht. w/stem 82", wire 15'.  
 Four candelabra base lamps,  
 each 60w max.

## SIX-LIGHT CHANDELIER

**P400113-143** Graphite  
 28" W., 15-5/8" ht.  
 Overall ht. w/stem 82", wire 15'.  
 Six candelabra base lamps,  
 each 60w max.

## SIX-LIGHT ISLAND

**P400114-143** Graphite  
 40" W., 15-5/8" ht., 15" d.  
 Overall ht. w/stem 82", wire 15'.  
 Six candelabra base lamps,  
 each 60w max.



P350121-009



P350121-104



P350121-109



P300214-143

P400113-143