

52" BUILDER WITH LIGHT KIT

A 52" two-light, five-blade fan with reversible blades and a beautifully crafted etched white glass bowl. Powerful AirPro motor features 3-speed, triple-capacitor control that can also be reversed to provide year-round comfort. Two medium-based LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30°)
- MDF/Plywood hybrid blades
- Etched white glass shade
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-5/8" ht.
80" lead wires

FINISHES

- Brushed Nickel - 09
- White - 30
- Architectural Bronze - 129



P2599-09
Brushed Nickel shown
with Cherry blades



P2599-09
Brushed Nickel shown
with Natural Cherry blades



Natural Cherry



Cherry



P2599-30
White shown
with White blades



White



White



P2599-129
Architectural Bronze shown
with Classic Walnut blades



Classic Walnut



Medium Cherry

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW: 4,474 cubic feet per minute
ELECTRICITY USE: 65 watts (excludes lights)
AIRFLOW EFFICIENCY: 68 cubic feet per minute per watt



Fan



Dry
Indoor only

LAMPING INFORMATION

Two medium base, 3000K, LED lamps included.
800 lumens/lamp, 80 CRI, non-dimmable.