

CORDIN

Featuring a striking combination of traditional and modern design, classic styling in the Cordin collection highlights a distinctive look for a variety of interiors. Elegant linear arms and a double-lined linen shade create a softer feel when combined with the vintage mechanical details and dual-tone frame. A Brushed Nickel finish with natural brass accents are incorporated in all fixtures in the Cordin family, including chandeliers, semi-flush, mini-pendant, island and swing arm options.



P400090-009



P710034-009



P400089-009



P500101-009



P400092-009



P350095-009



P400091-009

FINISH

● Brushed Nickel - 009

PAIR WITH

Hangar
Bonn
Hansford

SEMI-FLUSH CONVERTIBLE

P350095-009 Brushed Nickel
Hanging and ceiling mount hardware included.
16" dia., 12-1/2" ht.
Overall ht. w/stem 78", wire 10'.
Three medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER

P400089-009 Brushed Nickel
25" dia., 19" ht.
Overall ht. w/stem 85", wire 15'.
Three medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER

P400090-009 Brushed Nickel
30" dia., 20" ht.
Overall ht. w/stem 86", wire 15'.
Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER

P400091-009 Brushed Nickel
38" dia., 26" ht.
Overall ht. w/stem 92", wire 15'.
Nine medium base lamps, each 75w max.

THREE-LIGHT LINEAR CHANDELIER

P400092-009 Brushed Nickel
38" W., 10" L., 21" ht.
Overall ht. w/stem 87", wire 15'.
Three medium base lamps, each 75w max.

MINI-PENDANT

P500101-009 Brushed Nickel
10" dia., 8" ht.
Overall ht. w/stem 74", wire 10'.
One medium base lamp, 75w max.

WALL BRACKET

P710034-009 Brushed Nickel
10" W., 17-1/2" ht.
Extends 13-1/2". H/CTR 13-1/8".
Arm pivots 120°
One medium base lamp, 75w max.