

WEST VILLAGE

A modern form with industrial-inspired accents are featured in West Village. Double prismatic glass shades provide a beautiful illumination effect. Visual interest continues with a three-spoke frame that holds each glass shade. Antique Bronze with antique brass accents or Brushed Nickel with chrome accents provide touches of mixed metal in all fixtures within the collection.



ALSO AVAILABLE IN
Bath



P400009-020

PROGRESSLIGHTING.COM



P400008-020



P500006-020



P400010-020



P300004-020



P350032-020



P350032-020

FINISH

● Antique Bronze - 020

PAIR WITH

Union Square
Remix

WALL BRACKET

P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7" H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-020 Antique Bronze
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-020 Antique Bronze
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400009-020 Antique Bronze
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-020 Antique Bronze
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-020 Antique Bronze
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.

WEST VILLAGE

FINISH

- Brushed Nickel - 009

WALL BRACKET

P300004-009 Brushed Nickel
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-009 Brushed Nickel
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400009-009 Brushed Nickel
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-009 Brushed Nickel
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-009 Brushed Nickel
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.



P400009-009

PROGRESSLIGHTING.COM



P400008-009



P500006-009



P400010-009



P300004-009



P350032-009



P350032-009

WEST VILLAGE

Visual interest continues with a three-spoke design that holds each glass shade. Brushed Nickel with chrome accents or Antique Bronze with antique brass accents provide touches of mixed metal in all fixtures within the collection.

ALSO AVAILABLE IN
Collections



P300005-020



P300005-009



P300004-009



P300006-009



P300007-009



P300005-020



P300004-020



P300006-020



P300007-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300004-009 Brushed Nickel
P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300005-009 Brushed Nickel
P300005-020 Antique Bronze
14-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300006-009 Brushed Nickel
P300006-020 Antique Bronze
23-1/4" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300007-009 Brushed Nickel
P300007-020 Antique Bronze
32-1/4" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.