

STRATHAM

Stratham's signature focal point features a sparkly string of alternating drops of cylindrical and crystal orb beads. Large in scale, while delicate in details, the chandelier and semi-flush options showcase a stunning, faceted K9 glass column. Upward arching candelabra arms feature a soft Brushed Nickel finish and add visual interest for a variety of applications. Off white silk shades available separately for chandelier and semi-flush fixtures.



P400160-009
shown w/ P8704-01

PROGRESSLIGHTING.COM



P350118-009
shown as semi-flush



P350118-009



P710053-009



P400160-009



P400161-009

FINISH

● Brushed Nickel - 009

PAIR WITH

Carriage Hill
Glimmer
Celeste

SEMI-FLUSH CONVERTIBLE

P350118-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19" dia., 16-3/4" ht.
Overall ht. w/chain 56", wire 10'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400160-009 Brushed Nickel
27-1/4" dia., 25-1/2" ht.
Overall ht. w/chain 101", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400161-009 Brushed Nickel
Two-tier.
35-1/8" dia., 42" ht.
Overall ht. w/chain 164-1/2", wire 15'.
Nine candelabra base lamps,
each 60w max.

WALL BRACKET

P710053-009 Brushed Nickel
4-1/2" W., 14-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
One candelabra base lamp,
60w max.

ACCESSORY SHADE

P8704-01 White Fabric
1" uno-style fitter.
5-1/2" dia., 4-3/4" ht.



P8704-01