

BERGAMO

Bergamo features an elegant wispieness within a two-toned frame. Weathered stone accents and tassel details create a relaxed, rustic casual collection. These versatile pieces can be incorporated over a dining room table in a Rustic Farmhouse setting or in a Transitional open living space. Wall bracket, chandelier and foyer fixture options are available.



P400068-077



P400068-077



P710032-077

FINISH
● Forged Bronze - 077

PAIR WITH
Bowman
Gresham

FIVE-LIGHT CHANDELIER
P400068-077 Forged Bronze
26" dia., 27-7/8" ht.
Overall ht. w/chain 103", wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P400069-077 Forged Bronze
32" dia., 33-3/8" ht.
Overall ht. w/chain 108-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER
P400070-077 Forged Bronze
42-1/8" dia., 46-7/8" ht.
Overall ht. w/chain 170", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P500091-077 Forged Bronze
18-3/4" dia., 42-1/8" ht.
Overall ht. w/chain 117-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

WALL BRACKET
P710032-077 Forged Bronze
6" W., 17-1/4" ht.
Extends 7-5/8". H/CTR 6".
One candelabra base lamp,
60w max.



P400069-077



P500091-077



P400070-077