

WANDER

A Victorian-inspired bath and vanity collection, Wander wall brackets offer a clean and classic look. Etched glass shades are paired with a Polished Chrome, Brushed Nickel or Venetian Bronze finish to offer versatile styling for any home.



P300025-009



P300025-009



P300024-009



P300026-009



P300027-009

FINISH

● Brushed Nickel - 009

ONE-LIGHT BATH

P300024-009 Brushed Nickel
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300025-009 Brushed Nickel
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300026-009 Brushed Nickel
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300027-009 Brushed Nickel
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

WANDER

FINISH

- Polished Chrome - 015

ONE-LIGHT BATH

P300024-015 Polished Chrome
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.



P300024-015



P300025-015

TWO-LIGHT BATH

P300025-015 Polished Chrome
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300026-015 Polished Chrome
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.



P300026-015

FOUR-LIGHT BATH

P300027-015 Polished Chrome
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.



P300027-015

All fixtures mount up or down.

WANDER

FINISH

- Venetian Bronze - 074

ONE-LIGHT BATH

P300024-074 Venetian Bronze
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.



P300025-074



P300024-074

TWO-LIGHT BATH

P300025-074 Venetian Bronze
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.



P300026-074

THREE-LIGHT BATH

P300026-074 Venetian Bronze
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300027-074 Venetian Bronze
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.



P300027-074

All fixtures mount up or down.