

# CULLMAN

Cullman outdoor lanterns deliver dramatic scale with Craftsman appeal. Bold and linear details in an Antique Bronze finish highlight clear seeded glass. Ideal for spacious Modern architecture settings. Available in post, hanging and wall lantern options.



P560125-020



P560124-020



P560125-020



P560126-020



P550045-020



P540018-020

## FINISH

● Antique Bronze - 020

## POST LANTERN

**P540018-020** Antique Bronze  
11" sq., 22-3/4" ht.  
Fits 3" post (order separately).  
One medium base lamp,  
100w max.

## HANGING LANTERN

**P550045-020** Antique Bronze  
11" sq., 19-5/8" ht.  
Overall ht. w/chain 94", wire 10'.  
One medium base lamp,  
100w max.

## SMALL WALL LANTERN

**P560124-020** Antique Bronze  
7" W., 16-5/8" ht.  
Extends 8-3/8". H/CTR 2-3/8".  
One medium base lamp,  
100w max.

## MEDIUM WALL LANTERN

**P560125-020** Antique Bronze  
9" W., 16" ht.  
Extends 10-3/8". H/CTR 2-3/4".  
One medium base lamp,  
100w max.

## LARGE WALL LANTERN

**P560126-020** Antique Bronze  
11" W., 19-1/4" ht.  
Extends 12-1/2". H/CTR 2-3/4".  
One medium base lamp,  
100w max.