

VERDAE

Classic and formal clear seeded glass complements a Textured Black or Antique Bronze finish. Open bottom or hinged door provide easy access for cleaning and relamping.



P560016-020



P560014-020



P560014-031



P560015-020



P560015-031



P560016-020



P560016-031



P560017-020



P560017-031



P550002-020



P550002-031



P540002-020



P540002-031

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540002-020 Antique Bronze
P540002-031 Textured Black
 10-3/8" dia., 22-5/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.

HANGING LANTERN

P550002-020 Antique Bronze
P550002-031 Textured Black
 10-3/8" dia., 18-3/8" ht.
 Overall ht. w/chain 93-1/2"; wire 10'.
 Three candelabra base lamps,
 each 60w max.

SMALL WALL-LANTERN

P560014-020 Antique Bronze
P560014-031 Textured Black
 6-1/4" W., 13-1/4" ht.
 Extends 8-5/8". H/CTR 5-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560015-020 Antique Bronze
P560015-031 Textured Black
 8-1/4" W., 17-3/4" ht.
 Extends 11-3/8". H/CTR 10-1/8".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560016-020 Antique Bronze
P560016-031 Textured Black
 10-3/8" W., 21-3/4" ht.
 Extends 13-5/8". H/CTR 10".
 Three candelabra base lamps,
 each 60w max.

EXTRA-LARGE WALL-LANTERN

P560017-020 Antique Bronze
P560017-031 Textured Black
 10-3/8" W., 30-1/2" ht.
 Extends 13-1/4". H/CTR 14-3/4".
 Three candelabra base lamps,
 each 60w max.