




VERSA-CRIMP[®] HYDRAULIC COMPRESSION TOOL REMOTE-POWER OPERATED TYPE VC6FTR

TOOL
VC6FTRSP
AL/CU

- 750 MCM Al/Cu Max. Range
- Flip-top latch provides clear and easy removal from larger connectors and in limited spaces.

Includes:

- 3/8" male quick coupler
- High impact plastic carrying and shipping case
- Service manual
- 2-Year Warranty



Type VC6FTR

Note: Operates from hydraulic pump delivering 10,400 psi.

Conductor Range:

#10 Str. - 750 MCM Al/Cu

Approx. Weight Each:

6 lbs. (2.7 kg.)

VERSA-CRIMP[®] HYDRAULIC COMPRESSION TOOL REMOTE-POWER OPERATED TYPE VC6R

TOOL
VC6RSP
AL/CU

- Open head design allows for direct access to the connector in restricted areas.
- Readily adaptable for energized line use.
- 750 MCM Al/Cu max.

Includes:

- 3/8" male quick coupler
- High impact plastic carrying and shipping case
- Service manual
- 2-Year Warranty



Type VC6R

Note: Operates from hydraulic pump delivering 10,400 psi

Conductor Range:

#10 Str.—750 MCM Bare Al

#10 Str.—750 MCM Bare Cu

Approx. Weight Each:

5.5 lbs. (2.5 kg.)

DG
11