



VERSA-CRIMP® HYDRAULIC COMPRESSION TOOL HAND OPERATED TYPE VC7SP

TOOL
VC7SP
CU ONLY



- Open Head design allows direct access to the connector in restricted areas.
- Two Stage Pump Design allows nibs to travel from full open to full close much faster.
- Ergonomic Case has handle at balance point making tool much easier to carry.
- Range: #10 stranded to 750 MCM COPPER ONLY
- Head rotates 360°
- For compressing multi-strand/rope lay copper cable in mining, marine and industrial applications
- Copper label denotes copper connectors use only
- Repair parts available in kit form
- Direct Reading Pressure Gauge available
- 2-Year Warranty

Note: Due to high point pressure developed by this tool, it is not to be used on aluminum conductor or cable

What's in the Box:

Versa-Crimp® Tool
Ergonomic Case
Instruction/Parts Manual

Approx. Weight:

15.6 lbs. Gross
12.0 lbs. Tool Only

VERSA-CRIMP® HYDRAULIC COMPRESSION TOOL HAND OPERATED TYPE VC7FTSP

TOOL
VC7FTSP
CU ONLY



- The flip-top latch provides clear and easy removal from larger connectors in limited areas.
- Two Stage Pump Design allows nibs to travel from full open to full close much faster.
- Ergonomic Case has handle at balance point making tool much easier to carry.
- Range: #10 stranded to 750 MCM Al/CU
- Head rotates 360°
- For compressing multi-strand/rope lay copper cable in mining, marine and industrial applications
- Copper label denotes copper connectors use only
- Repair parts available in kit form
- Direct Reading Pressure Gauge available
- 2-Year Warranty

Note: Due to high point pressure developed by this tool, it is not to be used on aluminum conductor or cable

What's in the Box:

Versa-Crimp® Tool
Ergonomic Case
Instruction/Parts Manual

Approx. Weight:

15.6 lbs. Gross
12.0 lbs. Tool Only

DG
10