

## 20 Amp, 125/250, 3Ø 250 and 3Ø 480 Volts AC 3 Pole, 4 Wire, Grounding



20A 125/250V  
AC NEMA  
L14-20R  
2 (1) HP

20A 3Ø 250V  
AC NEMA  
L15-20R 3 HP

20A 3Ø 480V  
AC NEMA  
L16-20R 5 HP

### Connector Bodies

#### Watertight Safety-Shroud®

IP66 SUITABILITY

UL Type 4X, 12

| Description                               | Cord Dia.           | Catalog Number |           |           |
|-------------------------------------------|---------------------|----------------|-----------|-----------|
| Black Valox® housing, white Valox clamps. | .350"-1.150" (9-29) | HBL2413SW      | HBL2423SW | HBL2433SW |

#### Insulgrip®

IP20 SUITABILITY

| Description                                | Cord Dia.           | Catalog Number |           |           |
|--------------------------------------------|---------------------|----------------|-----------|-----------|
| Black and white nylon.                     | .350"-1.150" (9-29) | HBL2413        | HBL2423   | HBL2433   |
| Black and white nylon, spring termination. | .350"-1.150" (9-29) | HBL2413ST      | HBL2423ST | HBL2433ST |
| Spring termination, all black.             | .350"-1.150" (9-29) | HBL2413STBK    | —         | —         |
| Corrosion resistant, yellow nylon.         | .350"-1.150" (9-29) | HBL24CM13      | HBL24CM23 | HBL24CM33 |
| All black nylon.                           | .350"-1.150" (9-29) | HBL2413BK      | —         | —         |

Note: See pages C-52 and C-53 for accessories.

### Receptacles

#### Watertight Safety-Shroud

IP66 SUITABILITY

UL Type 4X, 12

| Description                                | Catalog Number |           |           |
|--------------------------------------------|----------------|-----------|-----------|
| Gray Valox housing and flange, back wired. | HBL2410SW      | HBL2420SW | HBL2430SW |

Note: See page C-54 for accessories.

#### Safety-Shroud® Twist-Lock®

IP20 SUITABILITY

| Description                                        | Catalog Number |            |            |
|----------------------------------------------------|----------------|------------|------------|
| Gray Valox angle housing, one gang, back wired.    | HBL2410AR      | HBL2420AR  | HBL2430AR  |
| Gray Valox surface mounting, one gang, back wired. | HBL2410SR      | HBL2420SR  | HBL2430SR  |
| Gray Valox semi-flush, two gang, back wired.       | HBL2410SR2     | HBL2420SR2 | HBL2430SR2 |

#### Single Flush Receptacles

IP20 SUITABILITY


| Description                                              | Catalog Number |           |           |
|----------------------------------------------------------|----------------|-----------|-----------|
| Black nylon face, back and side wired.                   | HBL2410        | HBL2420   | HBL2430   |
| Black and white nylon, spring termination.               | HBL2410ST      | HBL2420ST | HBL2430ST |
| Isolated ground, orange nylon face, back and side wired. | IG2410         | IG2420    | —         |
| Isolated ground, spring termination.                     | —              | IG2420ST  | —         |
| Ring terminal connection.                                | HBL2410RT      | HBL2420RT | —         |

Note: See page C-52 for accessories.


#### Insulgrip® Flanged Receptacles

| Description                                 | Catalog Number |           |           |
|---------------------------------------------|----------------|-----------|-----------|
| Nylon casing, back wired.                   | HBL2416        | HBL2426   | HBL2436   |
| Nylon casing, back wire, spring terminatio. | HBL2416ST      | HBL2426ST | HBL2436ST |


Note: See page C-52 for accessories.



HBL2416



HBL2410



HBL2420SR2




HBL2423SW




HBL2413



HBL2413ST



HBL2420SW



HBL2430ST



HBL2420SR

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.

Dimensions in Inches (mm)