

FEATURES

- Long-life LED is rated L90 at 60,000 hours
- Choice of three LED lumen packages
- Up to 112 lumens/watt efficacy on select packages
- Popular curved wall mount profile in solid or perforated housing
- 2½" × 6⅝" profile maintains a sleek aesthetic
- Companion fixture to Cûrv solid and perforated suspended luminaires
- Flat end caps standard, sculpted (SCE) or bull nose (BN) end caps are optional
- Installs easily using the universal wall mounting system (Wall bracket painted std. matte white unless otherwise specified)
- Constructed of heavy 20-gauge steel
- Patented die cast aluminum connection plates and end caps to ensure row integrity (Patent# 6,796,676B2)
- UL listed 1598, cUL or CSA, damp location listed
- Controls compatible for additional energy savings and code compliance
- Five year warranty (Terms and Conditions apply)



ORDERING INFORMATION


LCV	-	-	-	-	WM	-	-	-	U	-	-
MODEL	LED COLOR	LED LUMEN PACKAGE	MOUNTING METHOD	DRIVER	VOLTAGE	OPTIONS					
LCV Curv LED	30 3000K 35 3500K 40 4000K	LW Low Watt ML Medium Lumen HL High Lumen See Product Availability table below.	WM Wall Mount	E Fixed Output ED 0-10V Dimming	U 120V-277V	DC Dust Cover (N/A T5HO) ³ SCE Sculpted End Cap (5⅞") ³ BN Bull Nose End Cap (5⅞") ³ EMC One Emergency Circuit ^{1,2} NLC Night Light Circuit ^{1,2} GLR Fast Blow Fuse GTD Generator or Central Inverter supplied Lighting					
ROW LENGTH	HOUSING TYPE	FINISH									
4 4' Single 8 8' Single — Indicate row length over 8' in 4' increments Note: Rows over 8' will be configured by Alera. Example: 16' will be (2) 8'. Alternate configurations: contact factory.	PERF Perforated S Solid	MW Matte White (Std.) ZT ZET Metallic Silver See Color Selection Guide for other color selections.									

PRODUCT AVAILABILITY TABLE, 3000K

LUMEN PACKAGE	NOMINAL LUMENS	NOMINAL WATTS	LUMENS/ WATT
LW	3,150	30	105
ML	4,140	40	104
HL	4,870	50	97



¹ Not available with all configurations; some limitations apply.
² One feed drop per EMC or NLC. Contact factory for through wiring.
³ Ships separately.

CROSS SECTIONS



LCV WM

MOUNTING INFORMATION



Fixture brackets attach to universal wall mount bracket

DATA CHART

NOMINAL LENGTH	APPROX. WEIGHT (LBS.)	A*	B	C	D	E	F	G
4'	8	48⅞"	2⅓⅙"	42½"	24⅞"	27⅞"	1⅞"	3"
8'	16	96⅞"	2¾"	90⅞"	24⅞"	27⅞"	1⅞"	3"

*Note: Fixtures mounted in rows require two mounting locations per fixture. SCE end caps add 10⅞". BN adds 10⅞". Standard flat end caps add ⅝" to overall row length.