

12XPB Series

75 watt, 12VDC output, Hazardous Location Emergency System

FEATURES

- 'Normally off' emergency unit for explosion proof applications
- Self-contained battery and charger within a heavy-duty copper-free aluminum housing
- 12Vdc output with 75 watts to power 18 or 28 watt lamp-heads(sold separately)
- Includes Maintenance-free lead-acid batteries
- Temperature range: 20°C to 30°C (68°F to 86°F)
- UL 924 and 844 Listed for NEC C1D1 Groups C and D
- Includes Push-to-Test station and fittings for installation to main enclosure



EMERGENCY LIGHTING

ORDERING INFORMATION

12XPB

MODEL

75K

CAPACITY

75 Watts
for 90 mins

Blank

TIME DELAY RELAY

Blank No TDR
TDR120 120VAC input
TDR277 277VAC input

*To order the enclosure with charger and batteries only.

12XPB Plus Matching Fixtures

FEATURES

- EX-1CD ships with fittings kit for direct mount to the 12XPB75K(sold separately)
- REX-1 head designed for remote wall, ceiling or pendant mount
- Available with input voltage specific time delay relay to hold fixtures on for 15 minutes
- Available with 18 or 28 watt incandescent lamps
- Temperature code: T5 (100°C) for 40°C ambient in C1D1 Groups C,D
- Suitable for use in wet locations
- UL 924 and 844 Listed for NEC C1D1 Groups C and D



ORDERING INFORMATION

PART NUMBER	FIXTURE	INPUT VOLTAGE	LAMP WATTS	MOUNTING	HUB SIZE
93046917	EX-1CD1218	12VDC	18	Direct Mount	3/4"
93046918	EX-1CD1228		28		
93046908	REX1CDC120V	120VAC	up to 150W	Ceiling	
93046909	REX1CDC1218	12VDC	18		
93046910	REX1CDC1228		28		
93046911	REX1CDP120V	120VAC	up to 150W	Pendant	
93046912	REX1CDP1218	12VDC	18		
93046913	REX1CDP1228		28		
93046914	REX1CDW120V	120VAC	up to 150W	Wall	
93046915	REX1CDW1218	12VDC	18		
93046916	REX1CDW1228		28		

LUMINAIRE ACCESSORIES

MODEL	DESCRIPTION
EX100CD	Exit Sign Accessory
REX-AR	Angled Reflector
REX-SDR	Standard Reflector
XWG	Guard

ADDITIONAL MOUNTING OPTIONS

