

EVHCR

High Lumen LED Remote



FEATURES

- Twin head LED matching remote for the EVHC Series
- High lumen output, high mounting height application
- UV stable thermo-plastic construction in white finish
- Adjustable lamp-heads
- LED Lifetime Warranty

ORDERING INFORMATION

EVHCR2

MODEL

CAUTION: The EVHCR2 remote can only accept input power from the EVHC12 emergency light with remote capacity. The EVHCR2 will not work with any other emergency units.

INPUT POWER CONSUMPTION

- 18Vdc at 6 watts(3 watts per head) provided exclusively from the EVHC12 emergency light with remote capacity

SPECIFIC LED INFORMATION

- Lamp Color: Cool White
- Total Lamp Output: 326 lumens per lamp
- Rated LED Lamp-life: Greater than 100,000 hours

DIMENSIONS

