

Industrial Emergency Light



FEATURES

- High capacity emergency unit for commercial or industrial applications
- Black, corrosion-resistant, heavy gauge steel housing in 6, or 12 volt models
- Fully adjustable, glare free, high-output incandescent lamp heads
- High impact, 5VA flame rated, UV stabilized, black thermoplastic lamp heads
- Maintenance-free lead-acid battery with fully automatic charger
- 120/277 60 Hz VAC operation, test switch and LED AC-On indicator light
- Temperature range: 20°C to 30°C (68°F to 86°F)
- UL 924 Listed

ORDERING INFORMATION

AS		-		-	
MODEL	CAPACITY	OUTPUT VOLTAGE	SELF DIAGNOSTICS	OPTIONS	
	80 80 Watts	Blank 6 Volt	Blank None	V Voltmeter	
	130 130 Watts	12V 12 Volt ¹	I Spectron Self-test/ Self-diagnostic Electronics	3 3 Lampheads	
	180 180 Watts			0 0 Lampheads	
	270 270 Watts			1 1 Lampheads	
	360 360 Watts			C Ammeter ²	
				A31 Aux 3-conductor cord-120 volt	
				A32 Aux 3-conductor cord-277 volt	

¹Available on AS180, AS270 and AS360

²Not available with AS80 model

OPTIONAL LAMPS

AHDSB0608	6V, 8W Halogen
AHDSB0612	6V, 12W Halogen
AHDSB0618	6V, 18W Incandescent
AHDSB0620	6V, 20W Halogen
AHDSB0625	6V, 25W Incandescent
AHDSB1208	12V, 8W Halogen
AHDSB1212	12V, 12W Halogen
AHDSB1218	12V, 18W Incandescent
AHDSB1225	12V, 25W Incandescent
AHDSB1235	12V, 35W Incandescent
AHDSB1250	12V, 50W Halogen

To order two optional, non-standard lamps on the fixture, suffix catalog number.
Example: AS130-AHDSB0612.


ACCESSORIES

MODEL	DESCRIPTION
WB-6	Wall mounting hanger bracket; use with any AS model
6000	Heavy-duty mounting shelf for AS180 through AS 360
L-6	Mounting shelf for AS80 or AS130 only
40G	Wire guard
Matching Remote Fixtures	
SRHSB	Matching remote lighting head - single (black)*
SRHDB	Matching remote lighting head - twin (black)*

*Supplied with round mounting plate. Specify voltage and wattage when ordering.
Example: SRHDW1212. See "Remote Heads and Fixtures" section for available lamps.

SPECIFICATIONS

BASE CATALOG NUMBER	OUTPUT VOLTS	OUTPUT WATTS				STANDARD LAMP	REMOTE CAPABILITY
		1.5 HOURS	2 HOURS	3 HOURS	4 HOURS		
AS80	6	80	62	43	33	7.2W	Yes
AS130	6	130	101	70	54	7.2W	Yes
AS180-12V	12	180	144	112	77	7.2W	Yes
AS270-12V	12	270	227	168	116	7.2W	Yes
AS360-12V	12	360	288	230	172	7.2W	Yes



ELECTRONICS

- Transformer isolation, surge, transient and low voltage disconnect protection
- Reverse polarity, short circuit and AC lockout protection
- Extended remote capacity and time delay retransfer (TDR with Spectron only)

