

EBB Series

Hazardous Location Emergency Light

FEATURES

- Emergency luminaire in explosion proof applications
- Medium-Gray, epoxy-clad, copper-free aluminum housing
- Impact resistant, prismatic glass globes with incandescent lamps
- Temperature range: 0°C to 40°C (32°F to 104°F)
- UL 924 and 844 listed for NEC C1D1 & C1D2 Groups C & D, C2D1 & C2D2, C3D1 & C3D2



EMERGENCY LIGHTING


ORDERING INFORMATION

EBB				
MODEL	# OF LAMPS	WATTAGE	MOUNTING	HUB
	3 (3) Lamps	20 Watt	10A Pendant 10B Wall	2 3/4" Hub 3 1" Hub

¹10X Ceiling Mount option not available with 3/4" Hub Size

LUMINAIRE ACCESSORIES

MODEL	DESCRIPTION
VEXA400	Exit Accessory
EZG1	Globe Guard
VMPSD40	Dome Reflector
	Remote Test Station Included



Pendant			
A	B	C	D
22" (558mm)	21-1/4" (539mm)	11-1/4" (285mm)	18" (457mm)
Wall			
A	B	C	D
22-7/8" (580mm)	22-1/8" (561mm)	16-3/4" (425mm)	18" (457mm)