

Outdoor LED Remote

FEATURES

- Matching LED remote for the Evolution family
- High performance LEDs
- Architectural remote specifically for the Evolution family
- Durable Die-Cast Construction
- Fully gasketed, waterproof construction
- Single or Double Lamp-heads
- Corrosion resistant Black or White finish



REMOTE HEADS AND FIXTURES

ORDERING INFORMATION

EVO		
MODEL	HEADS	FINISH
	S Single	B Black
	D Double	W White


CAUTION: The EVO remote can only accept input power from the EV4D, EV4DI emergency light or EVC-D4 combo with remote capacity. The EVO will not work with any other emergency units.

INPUT POWER REQUIREMENTS

- 4.8Vdc at 1 watt per head provided exclusively from an EV4D or EV4DI emergency light with remote capacity

SPECIFIC LED INFORMATION

- Lamp color: Cool white
- Total lamp output: 88 lumens per head
- System Efficacy: 80 Lumens per LED
- Rated LED Lamplife: Greater than 100,000 hrs.



DIMENSIONAL NOTE

Dimensions reflect maximum fixture width and depth.