

PGF1

High Performance LED Sconce

EMERGENCY LIGHTING

FEATURES

- High performance LED wall-pack
- Sturdy, ADA compliant, vandal resistant, die-cast aluminum construction
- 7 long life 4300K high output LED's; 50,000 hours
- Wide area illumination with no heads to aim
- Dark Sky Compliant with use of supplied full cut-off shield
- Available with optional 120VAC photo-control
- Temperature range of -30° C to 50° C (-22° F to 22° F)
- Certified to UL1598 for use in wet locations
- U.S. Patent No. 0627,916



ORDERING INFORMATION


PGF1		-	
MODEL	FINISH		OPTIONS
	Z Dark Bronze		PC1 120VAC Photo-control
	P Platinum Silver		

INPUT POWER REQUIREMENTS

- 17.7 watts at 120/277VAC


SPECIFIC LED INFORMATION

- Lamp color: Cool white, 4300K
- Total lamp output: 1067 lumens
- LED Lamplife: 50,000 hrs.



7"

11"



3.19"