

## High Lumen Power Packs

### FEATURES

- High lumen power pack for use with linear, compact or long compact fluorescent lamps
- Compatible with electronic, magnetic, energy saving or dimming AC ballasts
- Sealed nickel-cadmium battery ; no AC ballast required for emergency only luminaires
- Can be used with switched or unswitched luminaires
- Installation may be on top of or remote from the luminaire
- Compatible with AC ballasts having End-of-Lamp-Life feature
- 120/277VAC 60Hz operation, test switch and AC-On indicator light
- Temperature range: 0°C to 40°C (32°F to 104°F)
- UL 924 Damp Location Listed



BATTERY PACKS

### ORDERING INFORMATION

**UFO-7W**

MODEL

SELF-DIAGNOSTICS

Blank None

- I Spectron Self-test/ Self-diagnostic Electronics

### SPECIFICATIONS

CATALOG NUMBER	INPUT WATTAGE	OUTPUT WATTAGE	LAMP TYPE	LAMP EXAMPLES	1 LAMP LUMENS	2 LAMP LUMENS
UFO-7W UFO-7WI	8	57.6	T5	FP28T5/HO	1850	--
				FP39T5/HO	2100	--
				FP54T5/HO	2650	--
				FPC55T5/HO	2300	--
			T8	F025, FB024 T8	2500	2600
				F032, FB031 T8	3000	3000
				F040 T8	2400	--
			T9 T10			
			T12	F40 T12, F40/U	3000	3000
				F40 T12ES (34W)	2700	2700
				F48 T12/HO	3000	--
				F96 T12	2800	--
				F96 T12/HO	2900	--
			Long CFL 4-pin	F96 T12/VHO	3300	--
				PL-L 24W, F27/24BX, DuLux L 27W	1800	2300
			CFL 4-pin	PL-L 36W, F39/36BX, DuLux L 39W	2900	3500
				PL-L 40W, F40/30BX, F50BX, DuLux L 55W	1800	--
2D 4-pin	PL-T 42W/4P	3200	3500			
	F282D/4P	2050	2800			
			F382D/4P	2800	2800	

### ACCESSORIES

MODEL	DESCRIPTION
F-WC	Wire bundle cover <sup>1</sup>
SPRTS	Remote test switch/charge indicator module <sup>2</sup>

<sup>1</sup>Encloses exposed wiring harness when power pack is externally mounted on the lighting fixture. One required per fixture.

<sup>2</sup>Fits single-gang box.

