

UFO-LED

LED Battery Pack

BATTERY PACKS



BATTERY PACKS

FEATURES

- Battery pack with 120/277 VAC 60Hz inverter output
- Sealed nickel-cadmium battery
- Can be used with switched or unswitched luminaires
- Installation may be within, or remote from the luminaire
- Indoor installation for indoor or outdoor luminaires
- 120/277 VAC 60 Hz input operation
- Remote test switch with AC-On indicator light
- Temperature range: 0°C to 45°C (32°F to 113°F); 20VA/W only for 45°-50°C (113°-122°F)
- UL 924 Damp Location Listed

ORDERING INFORMATION

UFO-LED

MODEL



CAPACITY
25 VA/W

ACCESSORIES

MODEL	DESCRIPTION
SPRTS	Remote test switch /charge indicator module ^{1,2}

¹Fits single-gang box
²Comes standard; additional may be ordered

SPECIFICATIONS

CATALOG NUMBER	INPUT WATTAGE	MAX. LOAD VA/W (UNITY PF)	LAMP TYPE
UFO-LED25	9.5	25	LED



SPRTS (INCLUDED REMOTE TEST SWITCH WITH CHARGING INDICATOR)

