


BL-PA2

Superbay Series

ACRYLIC



MOGUL BASE



Designed for lower wattage and lower mounting heights. BL-PA2 Series 16" diameter acrylic reflector combines attractive appearance with superb performance.

Up to 55°C ambient. Suitable for damp location. Minimum 90°C supply conductors.

Field-adjustable brackets allow for medium to wide lighting distributions. For best performance and visual comfort, coated lamps are recommended.

ORDERING INFORMATION

BL	-				-	PA2	-		-	EX
SERIES						OPTICS		COLOR		SOCKET
BL Superbay Series						PA2 16" Prismatic acrylic reflector		WH White (standard) GR Gray		EX Pink exclusionary socket. Required for PSMH
WATTAGE						VOLTAGE				
175 175w PSMH only						5 480V				
250 250w PSMH or HPS						8 Quad Tap® (120, 208, 240, 277V)				
320 320w PSMH only										
400 400w PSMH or HPS										

Wattage	BL-PA2 Open	BL-PA2 Enclosed
175 PSMH	55°C	40°C
250 PSMH/HPS	55°C	40°C
320 PSMH	55°C	40°C
400 PSMH/HPS	55°C	40°C


ACCESSORIES - Order Separately

Catalog Number	Description
BL-PK-ENC	Bottom acrylic enclosure
PA2-CDL	Conical bottom enclosure
PA2-DLR	Drop lens bottom enclosure

Note: Bottom enclosures are required unless lamps designated as "suitable for open use" are used
 Note: Options must be added as suffix to catalog number; Accessories must be ordered separately

For complete temperature information, see page 441.

For a complete list of **Options and Accessories** see pages 437 to 445.



	A	B	C	D	E	F
Quick-On®	22 1/8" - 22 7/8"	16 1/4"	8 5/8"	11"	9 1/2"	1 1/8"
	562 - 581 mm	413 mm	219 mm	279 mm	241 mm	29 mm
Slick-On®	24 1/2" - 25 1/4"	16 1/4"	9 1/2"	11"	9 1/2"	2"
	622 - 635 mm	413 mm	241 mm	279 mm	241 mm	51 mm