

COLT LED Bullet

LED bullet is versatile, compact flood-light for landscape, accent, pole, column, facade and small area illumination

- Replaces up to 70w HID or 84w CFL
- Traditional 1/2" x 14 NPS threaded adjustable knuckle mounting
- 120-277V operation
- 50/60HZ
- Die-cast aluminum housing
- Decorative dark bronze finish
- 3 distribution options in one carton (narrow, medium, wide)

- Rotatable hood for versatile glare control
- 3000K or 4000K color temperature
- IP65 and certified to UL 1598 for use in wet locations
- Certified up to 40°C ambient per UL 1598
- Accessory kits available for trunnion mount and color/tinted light applications



LANDSCAPE FLOOD

tradeSELECT[®]

Shown with Trunnion accessory

STOCK ORDERING INFORMATION

Catalog Number	Description	Finish	Weight lbs. (kg)	PKG. CODE
LED - Wet Location Listed - Universal Aiming				
BUL-1L3K-U	LED bullet flood, 3000K CCT	Bronze	5 (2.2)	FCC
BUL-1L4K-U	LED bullet flood, 4000K CCT	Bronze	5 (2.2)	FCC

PERFORMANCE INFORMATION

Series Number	Equivalency			Delivered Lumens	System Watts	Lumens Per Watt	Beam Pattern	CCT	Voltage	# of Drivers/ Current
	MH	HPS	CFL							
BUL-1L3K-U (wide)	70w	70w	84w	1802	21.2	85	3 x 3, 4 X 4, 6 X 6	3000K	120-277V	1@350mA
BUL-1L4K-U (wide)	70w	70w	84w	1886	21	90	3 x 3, 4 X 4, 6 X 6	4000K	120-277V	1@350mA
BUL-1L3K-U (narrow)	70w	70w	84w	1935	21.2	91	3 x 3, 4 X 4, 6 X 6	3000K	120-277V	1@350mA
BUL-1L4K-U (narrow)	70w	70w	84w	1965	21	93.5	3 x 3, 4 X 4, 6 X 6	4000K	120-277V	1@350mA

STOCK ACCESSORIES - Order Separately

Catalog Number	Description
BUL-COLOR	Lens kit with tinted color choices – Red, Blue, Green and Yellow
TRN-XX¹	Trunnion adaptor for 1/2" threaded knuckle mount

¹ Specify finish color to match fixture, e.g. DB - Bronze.




ADDITIONAL ACCESSORIES ON PG. 214-217

EQUIVALENCY INFORMATION

Equivalency			Energy Savings
MH	INC.	CFL	
150w	100w	84w	78%

DIMENSIONS



A	B	C
3"	6"	5"
76 mm	152 mm	127 mm

